



C7

by Burndy
Catalog ID: C7

Prop 65 Notice

Cast Bronze Clamp, Armored Cable to Water Pipe, 10 AWG - 2 AWG, 1-1/4" - 2" Water Pipe.

Features: For Connecting Armored Cable To Water Pipe, Zinc Plated Screws, D Indicates UL467 For Direct Burial In Earth And Concrete, Supplied With Silicon Bronze Hardware, Armored Cable: Yes, Ground Strap: No, Dimension C: 1 IN, Installation Torque: 50 IN-LB For Pipe Clamp And Wire Clamp, Length: 3.62 IN, Width: 0.94 IN, Water Pipe Size: 1-1/4 - 2 IN, Height: 2.38 IN

Product Details

General

Application	For Connecting Armored Cable To Water Pipe And Direct Burial In Earth And Concrete
Hardware Type	Zinc Plated
Material	Bronze Alloy
Material - Hardware	Zinc Plated Steel
Plated	Y
Plating Type	Zinc
Sub Brand	CLAMP
Type	Ground Clamp
UPC	781810142424
UPC 12 Digit	7818101424244

Dimensions

Dimension - Height inch	2.38 in
Dimension - L Length Overall mm	92 mm
Dimension - Length Overall inch	3.62 in
Dimension - Pad Width inch	1.00 in
Dimension - Width inch	0.94 in
Dimension - Width mm	24 mm

Conductor Related

Conductor - Armored Cable Size	Y
Conductor - Copper Solid Size	8 AWG;7 AWG;6 AWG;5 AWG;4 AWG;3 AWG;2 AWG
Conductor - Copper Solid Size Range	8 AWG-2 AWG
Conductor - Copper Str Size	10 AWG;9 AWG;8 AWG;7 AWG;6 AWG;5 AWG;4 AWG;3 AWG;2 AWG
Conductor - Copper Str Size Range	10 AWG-2 AWG

Conductor - Pipe EMT Size	1 1/4 in;1 1/2 in;2 in
Conductor - Pipe EMT Size Range	1 1/4 in-2 in
Conductor Type	<ul style="list-style-type: none"> • CU C Str-Size • CU C Solid-Size • Pipe EMT-Size

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)