

# CB23G19D09G4TN

by Burndy  
Catalog ID: CB23G19D09G4TN

Tin Plated Ferrules



## Product Details

### General

Connector Type	Braid
Material	Copper
Material - Ferrules	Y
Physical Attribute - Number of Braids	6
Plated	Y
UPC	781810264522
UPC 12 Digit	7818102645222

### Dimensions

Dimension - L Length Overall mm	485 mm
Dimension - Length Overall inch	19.09 in

### Electrical Ratings

Rating - Indoor Amperage	1500
--------------------------	------

### Certifications and Compliance

Certification - CSA Approved	No
Standards - RoHS Compliance Status	EX

### Logistics

Minimum Pack Quantity	1
-----------------------	---

**For further technical assistance, please contact us**

**BURNDY Headquarters**  
47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**  
8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)