



## CB3G24N

by Burndy  
Catalog ID: CB3G24N

Prop 65 Notice

Flexible Copper Covered Braid

## Product Details

### General

Connector Type	Braid
Material	Copper
Material - Ferrules	Y
Physical Attribute - Number of Braids	1
Plated	N
UPC	781810451588
UPC 12 Digit	7818104515888

### Dimensions

Dimension - Hole Size inch	0.56 in
Dimension - L Length Overall mm	610 mm
Dimension - Length Overall inch	24.00 in
Thickness - Pad	0.69 in

### Certifications and Compliance

Standards - RoHS Compliance Status	NC
------------------------------------	----

### Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

**BURNDY Headquarters**  
47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**  
8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)