



CB4E19D50G7TN

by Burndy
Catalog ID: CB4E19D50G7TN

Flexible Copper Covered Braid

Product Details

General

Connector Type	Braid
Insulation	Y
Material	Copper
Material - Ferrules	Y
Physical Attribute - Number of Braids	4
Plated	Y
UPC	781810353578
UPC 12 Digit	7818103535788

Dimensions

Dimension - L Length Overall mm	495 mm
Dimension - Length Overall inch	19.50 in

Electrical Ratings

Rating - Outdoor Amperage	800
---------------------------	-----

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	EX
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)