



CB4E79G8TN

by Burndy
Catalog ID: CB4E79G8TN

Tin Plated Ferrules

Product Details

General

Connector Type	Braid
Material	Copper
Material - Ferrules	Y
Physical Attribute - Number of Braids	4
Plated	Y
UPC	781810467954
UPC 12 Digit	7818104679544

Dimensions

Dimension - Hole Size inch	0.28 in
Dimension - L Length Overall mm	2007 mm
Dimension - Length Overall inch	79.00 in
Thickness - Pad	0.38 in

Certifications and Compliance

Standards - RoHS Compliance Status	UI
------------------------------------	----

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)