

CBD24N

by Burndy
Catalog ID: CBD24N

Prop 65 Notice

Insulated flexible tinned copper braid 24.00"x0.94"x0.13



Product Details

General

Connector Type	Braid
Material	Copper
Material - Ferrules	Copper
Physical Attribute - Number of Braids	1
UPC	781810544815
UPC 12 Digit	7818105448155

Dimensions

Dimension - L Length Overall mm	610
Dimension - Length Overall inch	24
Dimension - Width inch	0.94
Dimension - Width mm	24 mm

Electrical Ratings

Rating - Indoor Amperage	190 A
Rating - Outdoor Amperage	225 A

Certifications and Compliance

Certification - CSA Approved	No
Standards - RoHS Compliance Status	CM

Logistics

Minimum Pack Quantity	30
-----------------------	----

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)