

CBG13G6W

by Burndy
Catalog ID: CBG13G6W

Tin Plated Ferrules



Product Details

General

Connector Type	Braid
Insulation	Y
Material	Copper
Material - Ferrules	Y
Physical Attribute - Number of Braids	1
Plated	Y
UPC	781810452912
UPC 12 Digit	7818104529122

Dimensions

Dimension - L Length Overall mm	330 mm
Dimension - Length Overall inch	13.00 in

Electrical Ratings

Rating - Indoor Amperage	415
Rating - Outdoor Amperage	495

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	NC
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)