

## CCSC110800

by Burndy  
Catalog ID: CCSC110800

Clear Cold Shrink

- Length of tube is consistent before and after application
- Rip and Grip! Does not require heat gun or any installation tools
- Passes TELCORDIA GR-347-CORE Abrasion and Cut Test up to 750 kcmil
- Passes UL 746C Glow Wire Test
- Ripcord is recyclable



## Product Details

### General

|     |              |
|-----|--------------|
| UPC | 621945524200 |
|-----|--------------|

### Dimensions

|   |         |
|---|---------|
| Diameter                                    | 0.28 in |
| Dimension - Diameter Max before Shrink inch | 1.1     |
| Length                                      | 7.99 in |
| Width                                       | 0.12 in |

### Certifications and Compliance

|                              |    |
|------------------------------|----|
| Certification - CSA Approved | No |
|------------------------------|----|

### Logistics

|                       |        |
|-----------------------|--------|
| Carton Quantity       | 360 EA |
| Minimum Pack Quantity | 1      |

**For further technical assistance, please contact us**

**BURNDY Headquarters**  
47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**  
8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)