



CH10C0

by Burndy
Catalog ID: CH10C0

Nylon Cable Hanger

Product Details

General

| | |
|-----------------|--------------|
| Color | Black |
| Material | Nylon 6/6 |
| Mounting Method | Screw |
| UPC | 781810336403 |

Dimensions

| | |
|--------------------------------------|---------|
| Dimension - Bundle Diameter Max inch | 0.62 |
| Dimension - Width inch | 0.38 in |
| Dimension - Width mm | 10 mm |

Certifications and Compliance

| | |
|------------------------------------|-----|
| Certification - CSA Approved | No |
| Certification - ETL | No |
| Certification - UL Recognized | No |
| Certification - UV Rated | Yes |
| Certification - cULus | No |
| Standards - RoHS Compliance Status | CM |
| UL Listed | No |

Logistics

| | |
|-----------------------|------|
| Carton Quantity | 1000 |
| Minimum Pack Quantity | 1000 |
| Packaging Type | Bag |

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)