

## CKSU22

by Burndy  
Catalog ID: CKSU22

Prop 65 Notice

Universal SERVIT W/SC2 Cover Accom: Equal Run & Tap: 10 SOL-2 SOL  
UL Listed For Cu Only Torque: 275 lb-in Metric Range: 6mm-25mm, TRQ:  
31Nm



## Product Details

### General

Connector Type	Split Bolt
Material	Copper
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	SERVIT®
UPC	781810294901
UPC 12 Digit	7818102949011

### Conductor Related

Conductor Type	<ul style="list-style-type: none"> <li>• CU C Solid-Run</li> <li>• CU C Str-Run</li> <li>• AL C Str-Run</li> <li>• AAAC C 5005-Run</li> <li>• AAAC C 6201-Run</li> <li>• ACSR C Str-Run</li> <li>• CU C Solid-Tap</li> <li>• CU C Str-Tap</li> <li>• AL C Str-Tap</li> <li>• AAAC C 5005-Tap</li> <li>• AAAC C 6201-Tap</li> <li>• ACSR C Str-Tap</li> <li>• GAL Steel C Str-Size</li> </ul>
----------------	--

### Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

### Logistics

**For further technical assistance, please contact us**

**BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)