

CL1/014TN

by Burndy
Catalog ID: CL1/014TN

Prop 65 Notice

COPPER LAY-IN-LUG WIRE RANGE: 1/0 - 14 STEEL SET SCREW TIN PLATED



Product Details

General

Plated	Y
Plating Type	Tin
Trade Name	QIKLUG™
UPC	781810505144
UPC 12 Digit	7818105051444

Dimensions

Dimension - Height inch	1.17 in
Dimension - Hole Size inch	0.27 in
Dimension - Length Overall inch	1.50 in
Dimension - Pad Width inch	0.60 in
Dimension - Width inch	0.60 in

Conductor Related

Conductor - Copper Solid Size	14 AWG;13 AWG;12 AWG;11 AWG;10 AWG;9 AWG;8 AWG;7 AWG;6 AWG;5 AWG;4 AWG;3 AWG;2 AWG;1 AWG;1/0 AWG
Conductor - Copper Solid Size Range	14 AWG-1/0 AWG
Conductor - Copper Str Size	14 AWG;12 AWG;10 AWG;9 AWG;8 AWG;7 AWG;6 AWG;5 AWG;4 AWG;3 AWG;2 AWG;1 AWG;1/0
Conductor - Copper Str Size Range	14 AWG-1/0

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	240 EA
Minimum Pack Quantity	1

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)