



CL3/0516TN

by Burndy
Catalog ID: CL3/0516TN

COPPER LAY-IN-LUG WIRE RANGE: 3/0 - #6 STEEL SET SCREW TIN PLATED

Product Details

General

Plated	Y
Plating Type	Tin
Trade Name	QIKLUG™
UPC	781810505151
UPC 12 Digit	7818105051511

Dimensions

Dimension - Height inch	1.56 in
Dimension - Hole Size inch	0.33 in
Dimension - Length Overall inch	2.00 in
Dimension - Pad Width inch	0.80 in
Dimension - Width inch	0.80 in

Conductor Related

Conductor - Copper Solid Size	6 AWG;5 AWG;4 AWG;3 AWG;2 AWG;1 AWG;1/0 AWG;2/0 AWG;3/0 AWG
Conductor - Copper Solid Size Range	6 AWG-3/0 AWG
Conductor - Copper Str Size	6 AWG;5 AWG;4 AWG;3 AWG;2 AWG;1 AWG;1/0 ;2/0 AWG;3/0 AWG
Conductor - Copper Str Size Range	6 AWG-3/0 AWG

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	90 EA
Minimum Pack Quantity	1

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)