



CL501RK

by Burndy
Catalog ID: CL501RK

Prop 65 Notice

High Strength Pure Electrolytic Copper Body Lug, Open-Faced, Conductor Range: 14 AWG-4 AWG.

Features: The Lay-In QIKLUG is manufactured from high strength pure electrolytic copper to ensure maximum strength and conductivity, UL467 listed for direct burial in earth or concrete, the open-faced design allows for fast lay-in of the conductor without the need for cutting or breaking, Height: 0.85 IN, Length: 1.13 IN, Width: 0.38 IN Pad, Stud Size: #10, Installation Torque: Yes, Set Screw Type: Slot, Package: Clamshell

Product Details

General

Application	For Direct Burial Applications In Concrete Or Earth, For Fast Lay-In Of The Conductor Without The Need For Cutting Or Breaking
Plating Type	Tin - Electro Plated
Sub Brand	QIKLUG
Trade Name	QIKLUG™
Type	Open-Faced
UPC	781810359754
UPC 12 Digit	7818103597544

Dimensions

Dimension - Hole Size inch	0.22 in
Dimension - Length Overall inch	1.13 in

Conductor Related

Conductor - Copper Solid Size	14 AWG;13 AWG;12 AWG;11 AWG;10 AWG;9 AWG;8 AWG;7 AWG;6 AWG;5 AWG;4 AWG
Conductor - Copper Solid Size Range	14 AWG-4 AWG
Conductor - Copper Str Size	14 AWG;12 AWG;10 AWG;9 AWG;8 AWG;7 AWG;6 AWG;5 AWG;4 AWG
Conductor - Copper Str Size Range	14 AWG-4 AWG

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - cULus	Yes
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	10
Number of Pieces in Package	3

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)