



CL501TNBULK

by Burndy
Catalog ID: CL501TNBULK

QIKLUG, LAY-IN LUG - BULK VERSION 14-10 AWG20 lb-in Torque 8
AWG25 lb-in Torque 6-4 AWG35 lb-in Torque

Product Details

General

Material	Copper
Material - Hardware	Stainless Steel
Plated	Y
Plating Type	Tin
Trade Name	QIKLUG™
UPC	781810492796
UPC 12 Digit	7818104927966

Dimensions

Dimension - D inch	0.47 in
Dimension - Height inch	0.85 in
Dimension - Hole Size inch	0.22 in
Dimension - Length Overall inch	1.13 in
Dimension - N inch	0.19 in
Dimension - Stud Size inch	17/64
Dimension - Width inch	0.38 in

Conductor Related

Conductor - Copper Str Size	14 AWG;12 AWG;10 AWG;9 AWG;8 AWG;7 AWG;6 AWG;5 AWG;4 AWG
Conductor - Copper Str Size Range	14 AWG-4 AWG

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	500 EA
Minimum Pack Quantity	500

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)