

CP26A26A

by Burndy
Catalog ID: CP26A26A

Prop 65 Notice

ACSR, 6201, 5005: 1/0 CU. & ALUM.: 3/0 SOL - 2/0 STR. GROOVE A
GROOVE B



Product Details

General

Material	Aluminum
Plated	N
Plating Type	Unplated
UPC	781810012963
UPC 12 Digit	7818100129633

Dimensions

Dimension - B Length inch	4 in
Dimension - Height fraction	2-7/8 in
Dimension - Height inch	2.875 in
Dimension - Width fraction	2-1/8 in
Dimension - Width inch	2.09 in
Dimension - Width mm	54 mm

Conductor Related

Conductor - ACSR Str Size	6 (6/1) Turkey AWG
Conductor - ACSR Str Size Range	6 (6/1) Turkey AWG
Conductor - AL Str Size A	2/0 AWG;3/0 AWG
Conductor - AL Str Size A Range	2/0 AWG-3/0 AWG
Conductor - AL Str Size B	2/0 AWG;3/0 AWG
Conductor - AL Str Size B Range	2/0 AWG-3/0 AWG
Conductor - Copper Str Size A	2/0 AWG;3/0 AWG
Conductor - Copper Str Size A Range	2/0 AWG-3/0 AWG
Conductor - Copper Str Size B	2/0 AWG;3/0 AWG
Conductor - Copper Str Size B Range	2/0 AWG-3/0 AWG

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM

UL Listed

No

Logistics

Minimum Pack Quantity

10

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)