

CP28A28A

by Burndy
Catalog ID: CP28A28A

Prop 65 Notice

ACSR,6201,5005: 3/0, 134.6(12-7) CU.& ALUM.: 4/0 STR. GROOVE A
GROOVE B



Product Details

General

Installation Torque Recommended in-lb	300 LBS/in
Material	Aluminum
Plated	N
Plating Type	Unplated
UPC	781810012994
UPC 12 Digit	7818100129944

Dimensions

Dimension - B Length inch	4 in
Dimension - Height fraction	2-7/8 in
Dimension - Height inch	2.875 in
Dimension - Width fraction	2-1/8 in
Dimension - Width inch	2.09 in
Dimension - Width mm	54 mm

Conductor Related

Conductor - ACSR Str Size	134.6 (12/7) Leghorn kcmil
Conductor - ACSR Str Size Range	134.6 (12/7) Leghorn kcmil
Conductor - AL Str Size A	4/0 AWG
Conductor - AL Str Size A Range	4/0 AWG
Conductor - AL Str Size B	4/0 AWG
Conductor - AL Str Size B Range	4/0 AWG
Conductor - Copper Str Size A	4/0 AWG
Conductor - Copper Str Size A Range	4/0 AWG
Conductor - Copper Str Size B	4/0 AWG
Conductor - Copper Str Size B Range	4/0 AWG

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No

Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	10
-----------------------	----

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)