

CP29A29A

by Burndy
Catalog ID: CP29A29A

Prop 65 Notice

High strength, high conductivity aluminum body and hardware provide corrosion resistant assembly. Recommended for tap or parallel connections



Product Details

General

Installation Torque Recommended in-lb	300 LBS/in
Material	Aluminum
Plated	N
Plating Type	Unplated
UPC	781810013007
UPC 12 Digit	7818100130077

Dimensions

Dimension - B Length inch	4 in
Dimension - Height fraction	2-7/8 in
Dimension - Height inch	2.875 in
Dimension - Width fraction	2-1/8 in
Dimension - Width inch	2.125 in

Conductor Related

Conductor - ACSR Str Size	159 (12/7) Guinea kcmil;176.9 (12/7) Dotterel kcmil;190.8 (12/7) Dorking kcmil;211.3 (12/7) Cochin kcmil;203.2 (16/9) Brahma kcmil
Conductor - ACSR Str Size Range	159 (12/7) Guinea kcmil-203.2 (16/9) Brahma kcmil
Conductor - AL Str Size A	250 kcmil;266 kcmil
Conductor - AL Str Size A Range	250 kcmil-266 kcmil
Conductor - AL Str Size B	250 kcmil;266 kcmil
Conductor - AL Str Size B Range	250 kcmil-266 kcmil
Conductor - Copper Str Size A	250 kcmil
Conductor - Copper Str Size A Range	250 kcmil
Conductor - Copper Str Size B	250 kcmil
Conductor - Copper Str Size B Range	250 kcmil

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No

Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	10
-----------------------	----

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)