

CP30A30A

by Burndy
Catalog ID: CP30A30A

Prop 65 Notice

ACSR,6201.5005: 176.9,190.8,266.8 CU.& ALUM.: 300 GROOVE A GROOVE B



Product Details

General

Installation Torque Recommended in-lb	300 LBS/in
Material	Aluminum
Plated	N
Plating Type	Unplated
UPC	781810012949
UPC 12 Digit	7818100129499

Dimensions

Dimension - B Length fraction	4-1/2 in
Dimension - B Length inch	4.50 in
Dimension - Height fraction	2-7/8 in
Dimension - Height inch	2.875 in
Dimension - Width fraction	2-3/8 in
Dimension - Width inch	2.375 in

Conductor Related

Conductor - ACSR Str Size	176.9 (12/7) Dotterel kcmil;190.8 (12/7) Dorking kcmil;211.3 (12/7) Cochin kcmil;203.2 (16/9) Brahma kcmil;266.8 (18/1) Waxwing kcmil;266.8 (26/7) Owl kcmil;266.8 (26/7) Partridge kcmil
Conductor - ACSR Str Size Range	176.9 (12/7) Dotterel kcmil-266.8 (26/7) Partridge kcmil
Conductor - AL Str Size A	300 kcmil
Conductor - AL Str Size A Range	300 kcmil
Conductor - AL Str Size B	300 kcmil
Conductor - AL Str Size B Range	300 kcmil
Conductor - Copper Str Size A	300 kcmil
Conductor - Copper Str Size A Range	300 kcmil
Conductor - Copper Str Size B	300 kcmil
Conductor - Copper Str Size B Range	300 kcmil

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No

Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	3
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)