

CP32A32A

by Burndy
Catalog ID: CP32A32A

Prop 65 Notice

ACSR,6201,5005: 203.2,336.4,397.5 CU. & ALUM.: 397.5,400 GROOVE A
GROOVE B



Product Details

General

Installation Torque Recommended in-lb	300 LBS/in
Material	Aluminum
Plated	N
Plating Type	Unplated
UPC	781810012987
UPC 12 Digit	7818100129877

Dimensions

Dimension - B Length inch	5 in
Dimension - Height fraction	3 in
Dimension - Height inch	3 in
Dimension - Width fraction	2-1/2 in
Dimension - Width inch	2.50 in

Conductor Related

Conductor - ACSR Str Size	203.2 (16/9) Brahma kcmil;266.8 (18/1) Waxwing kcmil;266.8 (26/7) Owl kcmil;266.8 (26/7) Partridge kcmil;300.0 (26/7) Ostrich kcmil;336.4 (18/1) Merlin kcmil;336.4 (26/7) Linnet kcmil;336.4 (30/7) Oriole kcmil;397.5 (18/1) Chickadee kcmil
Conductor - ACSR Str Size Range	203.2 (16/9) Brahma kcmil-397.5 (18/1) Chickadee kcmil
Conductor - AL Str Size A	397 kcmil;400 kcmil
Conductor - AL Str Size A Range	397 kcmil-400 kcmil
Conductor - AL Str Size B	397 kcmil;400 kcmil
Conductor - AL Str Size B Range	397 kcmil-400 kcmil
Conductor - Copper Str Size A	400 kcmil
Conductor - Copper Str Size A Range	400 kcmil
Conductor - Copper Str Size B	400 kcmil
Conductor - Copper Str Size B Range	400 kcmil

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No

Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	5
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)