

CP36A36A

by Burndy
Catalog ID: CP36A36A

Prop 65 Notice

CABLE GROOVE A AL. - CU 600 ACS GROOVE B AL.-CU 600 ACS



Product Details

General

| | |
|---------------------------------------|---------------|
| Installation Torque Recommended in-lb | 300 LBS/in |
| Material | Aluminum |
| Plated | N |
| Plating Type | Unplated |
| UPC | 781810080986 |
| UPC 12 Digit | 7818100809866 |

Dimensions

| | |
|---------------------------------|------|
| Dimension - Length Overall inch | 5.25 |
|---------------------------------|------|

Conductor Related

| | |
|-------------------------------|-----------------------|
| Conductor - ACSR Str Size | 477 kcmil |
| Conductor - AL Str Size Range | 550 kcmil - 600 kcmil |

Certifications and Compliance

| | |
|------------------------------------|----|
| Certification - CSA Approved | No |
| Certification - ETL | No |
| Certification - UL Recognized | No |
| Certification - cULus | No |
| Standards - RoHS Compliance Status | CM |
| UL Listed | No |

Logistics

| | |
|-----------------------|---|
| Minimum Pack Quantity | 6 |
|-----------------------|---|

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)