

CP37A37A

by Burndy
Catalog ID: CP37A37A

Prop 65 Notice

ACSR,6201,5005: 500,556.5,636,605 CU. & ALUM.: 636 GROOVE A
GROOVE B



Product Details

General

Installation Torque Recommended in-lb	300 LBS/in
Material	Aluminum
Plated	N
Plating Type	Unplated
UPC	781810012932
UPC 12 Digit	7818100129322

Dimensions

Dimension - B Length fraction	5-1/4 in
Dimension - B Length inch	5.25 in
Dimension - Height fraction	3-3/8 in
Dimension - Height inch	3.375 in
Dimension - Length Overall inch	5.25
Dimension - Width inch	3 in

Conductor Related

Conductor - ACSR Str Size	556.5 (24/7) Parakeet kcmil;556.5 (26/7) Dove kcmil;556.5 (30/7) Eagle kcmil;605 (24/7) Peacock kcmil
Conductor - ACSR Str Size Range	500 kcmil - 605 kcmil
Conductor - AL Str Size A	636 kcmil
Conductor - AL Str Size A Range	636 kcmil
Conductor - AL Str Size B	636 kcmil
Conductor - AL Str Size B Range	636 kcmil
Conductor - AL Str Size Range	636 kcmil
Conductor - Copper Str Size A	600 kcmil
Conductor - Copper Str Size A Range	600 kcmil
Conductor - Copper Str Size B	600 kcmil
Conductor - Copper Str Size B Range	600 kcmil

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No

Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	3
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)