

CP39A39ASS

by Burndy
Catalog ID: CP39A39ASS

Prop 65 Notice

Substation Connectors



Product Details

General

Application	Substation
Connector Type	Spacer
Installation Torque Recommended in-lb	480 lb-in
Material	Aluminum Alloy, Cast
Material - Hardware	Stainless Steel
Plated	N
Plating Type	Unplated
UPC	781810499405
UPC 12 Digit	7818104994055

Dimensions

Dimension - Height inch	3.32 in
Dimension - L Length Overall mm	133.35 mm
Dimension - Length Overall inch	5.25 in
Dimension - Width mm	76 mm

Electrical Ratings

Rating - KVA	230 kV
--------------	--------

Conductor Related

Conductor - ACSR Str Size	605 (26/7) kcmil;636 (24/7) kcmil;636 (26/7) kcmil;605 (30/19) kcmil;665.6 (24/7) kcmil;636 (30/19) kcmil
Conductor - ACSR Str Size Range	605 (26/7) kcmil-665.6 (24/7) kcmil
Conductor - AL Str Size	700 kcmil;715.5 kcmil;750 kcmil
Conductor - AL Str Size Range	700 kcmil-715.5 kcmil
Physical Attribute - Number of Conductors Accommodated Total	2

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	90
-----------------------	----

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)