

CP3R445A4

by Burndy
Catalog ID: CP3R445A4

Substation Connectors



Product Details

General

Application	Substation
Connector Type	Spacer
Installation Torque Recommended in-lb	480 lb-in
Material	Aluminum Alloy, Cast
Material - Hardware	Aluminum
Plated	N
Plating Type	Unplated
UPC	781810491348
UPC 12 Digit	7818104913488

Dimensions

Dimension - B Length inch	3.00 in
Dimension - Height inch	2.54 in
Dimension - L Length Overall mm	248 mm
Dimension - Length Overall inch	9.76 in
Dimension - Width mm	76 mm

Electrical Ratings

Rating - KVA	345 kV
--------------	--------

Conductor Related

Conductor - ACSR Str Size	900 (54/7) Canary kcmil;954 (45/7) Rail kcmil;954 (54/7) Cardinal kcmil;1033.5 (45/7) Ortolan kcmil
Conductor - ACSR Str Size Range	900 (54/7) Canary kcmil-1033.5 (45/7) Ortolan kcmil
Conductor - AL Str Size	1000 kcmil;1033 kcmil;1100 kcmil;1113 kcmil
Conductor - AL Str Size Range	1000 kcmil-1113 kcmil

Conductor Type	<ul style="list-style-type: none"> • AL C Str-Size • ACSR C Str-Size
Physical Attribute - Number of Conductors Accommodated Total	3

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)