

CSB163900SR1

by Burndy
Catalog ID: CSB163900SR1

In-line splice sealing kit, Conductor range- 1200-200,
Supplied tube length- 7.5", Relaxed tube length- 9.00".



Product Details

General

| | |
|-----|--------------|
| UPC | 621945442009 |
|-----|--------------|

Conductor Related

| | |
|----------------|----------|
| Conductor Size | 1200-200 |
|----------------|----------|

Certifications and Compliance

| | |
|------------------------------------|----|
| Certification - CSA Approved | No |
| Standards - RoHS Compliance Status | CM |

Logistics

| | |
|-----------------------|---|
| Minimum Pack Quantity | 1 |
|-----------------------|---|

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)