



## CT110200SSBC

by Burndy  
Catalog ID: CT110200SSBC

Nylon Stainless Steel BARB Cable Ties, 8.7 IN L, .28 IN W, Tensile Strength: 110 Lbs, Color: Natural.

- Stainless Steel Barb Tie  
Nylon 6/6 Standard, Self-locking stainless steel barb, Maximum strength and adjustability for versatility

### Product Details

#### General

Application	For use with self-locking stainless steel barb
Color	Natural
Material	Nylon 6/6
Rating - Minimum Tensile Strength lbs	110 lb
Sub Brand	UNIRAP,CABLE TIE
Trade Name	UNIRAP™
Type	CT_SSB
UPC	781810564769

#### Dimensions

Dimension - Bundle Diameter Max inch	2.01
Dimension - L Length Overall mm	221 mm
Dimension - Length Overall inch	8.70 in
Dimension - Width inch	0.28 in
Dimension - Width mm	7 mm

#### Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - cULus	Y
Standards - RoHS Compliance Status	CM

#### Logistics

Carton Quantity	5000 EA
Minimum Pack Quantity	100

**For further technical assistance, please contact us**

**BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)