



CT110325SSBC0

by Burndy
Catalog ID: CT110325SSBC0

Nylon 6/6 UV Stabilized Cable Tie with Stainless Steel Barb, 110 Lbs, UV Resistant Black, 3.15" Bundle Dia., Package: 100.

- Stainless Steel Barb Tie
Nylon 6/6 Standard, Self-locking stainless steel barb, Maximum strength and adjustability for versatility, Chemically resistant to solvents,oils,grease,and diluted acids, Rounded edges and bent tail for easy installation, Safe for air handling spaces

Product Details

General

Application	For use with self-locking stainless steel barb
Color	Black
Rating - Minimum Tensile Strength lbs	110 lb
Sub Brand	UNIRAP,CABLE TIE
Trade Name	UNIRAP™
Type	CT_SSB
UPC	781810564790

Dimensions

Dimension - Bundle Diameter Max inch	3.15
Dimension - L Length Overall mm	300 mm
Dimension - Length Overall inch	11.81 in
Dimension - Width inch	0.28 in
Dimension - Width mm	7 mm

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - cULus	Y
Standards - RoHS Compliance Status	CM

Logistics

Carton Quantity	5000 EA
Minimum Pack Quantity	100

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)