



CT120200D0

by Burndy
Catalog ID: CT120200D0

Nylon UNIRAP - 120 Lb. Tensile Strength

- Standard Cable Tie

Product Details

General

Color	Black
Material	Nylon 6/6
Operating Temperature Celcius Max	85 °C
Operating Temperature Celcius Min	-40 °C
Rating - Minimum Tensile Strength lbs	120
Trade Name	UNIRAP™
UPC	781810333457

Dimensions

Dimension - Bundle Diameter Max inch	2
Dimension - L Length Overall mm	221 mm
Dimension - Length Overall inch	8.70 in
Dimension - Width inch	0.3 in
Dimension - Width mm	8 mm

Certifications and Compliance

Certification - 94V0 Rated	N
Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - UV Rated	Yes
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	2500 EA
Minimum Pack Quantity	500
Packaging Type	Bag

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)