



CT120200LO

by Burndy
Catalog ID: CT120200LO

UV Black Nylon 6/6 Cable Tie, 2" Max. Bundle Dia, 120 Lbs, 8.87" Long, 0.30" Wide.

- Standard Cable Tie
- Features: Cable Ties for General Use Available in Black or Natural, One piece injection molded, Installation Tool: TWT2, MK9 Tool

Product Details

General

Application	For Outdoor Applications
Color	UV Black
Material	Nylon 6/6
Operating Temperature Celcius Max	85 °C
Operating Temperature Celcius Min	-40 °C
Rating - Minimum Tensile Strength lbs	120
Sub Brand	UNIRAP,CABLE TIE
Tool Type	Standard
Trade Name	UNIRAP™
Type	Standard
UPC	781810333440

Dimensions

Dimension - Bundle Diameter Max inch	2
Dimension - L Length Overall mm	229 mm
Dimension - Length Overall inch	9 in
Dimension - Width inch	0.30 in
Dimension - Width mm	8 mm

Certifications and Compliance

Certification - 94V0 Rated	N
Certification - CSA Approved	No
Certification - UV Rated	Yes
Standards - RoHS Compliance Status	CM

Logistics

Carton Quantity	2500 EA
Minimum Pack Quantity	50

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)