

CT120200L2

by Burndy
Catalog ID: CT120200L2

Nylon UNIRAP - 120 Lb. Tensile Strength

- Standard Cable Tie



Product Details

General

Color	Red
Material	Nylon 6/6
Rating - Minimum Tensile Strength N	120
Trade Name	UNIRAP™
UPC	781810332948
UPC 12 Digit	7818103329488

Dimensions

Dimension - Bundle Diameter Max inch	2
Dimension - L Length Overall mm	225 mm
Dimension - Length Overall inch	8.87 in
Dimension - Width fraction	3/10 in
Dimension - Width inch	0.3 in
Dimension - Width mm	8 mm

Certifications and Compliance

Certification - 94V0 Rated	N
Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - UV Rated	No
Certification - cULus	No
Standards - RoHS Compliance Status	UI
UL Listed	No

Logistics

Carton Quantity	1000 EA
Minimum Pack Quantity	20000

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)