


# CT120200L

by Burndy  
Catalog ID: CT120200L

Nylon UNIRAP - 120 Lb. Tensile Strength

- Standard Cable Tie



## Product Details

### General

Color	Natural
Installation Torque Recommended in-lb	12 LBS/in
Material	Nylon 6/6
Operating Temperature Celcius Max	85 °C
Operating Temperature Celcius Min	-40 °C
Rating - Minimum Tensile Strength lbs	120
Tool Type	Standard
Trade Name	UNIRAP™
UPC	781810332924

### Dimensions

Dimension - Bundle Diameter Max inch	2
Dimension - L Length Overall mm	221 mm
Dimension - Length Overall inch	8.70 in
Dimension - Width inch	0.30 in
Dimension - Width mm	8 mm

### Certifications and Compliance

Certification - 94VO Rated	N
Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - UV Rated	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

### Logistics

Carton Quantity	2500 EA
Minimum Pack Quantity	1000
Packaging Type	Bag

**For further technical assistance, please contact us**

**BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)