


## CT120300L

by Burndy  
Catalog ID: CT120300L

Nylon UNIRAP - 120 Lb. Tensile Strength

- Standard Cable Tie



## Product Details

### General

Color	Red
Item Type	Switch Accessories
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Performance	Environmental - Operating Temperatures - Max Continuous -75°C, Minimum- -40°C Without Impact
Series	Red Neon Pilot Light
UPC	783585431307 781810333044

### Dimensions

Dimension - Width inch	0.30 in
Height	1.47 in
Length	4.09 in
Weight	0.2 lb
Width	1.31 in

### Electrical Ratings

Connectivity	Side Wired Only
Voltage Rating	120-277 VAC

### Certifications and Compliance

Certification - 94V0 Rated	N
Certification - CSA Approved	No
Certification - cULus	No
Industry Standard(s)	UL Listed
UL Listed	No

### Logistics

Carton Quantity	2000 EA 10 EA
Minimum Pack Quantity	50

For further technical assistance, please contact us

**BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)