



CT120300SSBLO

by Burndy
Catalog ID: CT120300SSBLO

Nylon Stainless Steel BARB Cable Ties, 11.81 IN L, .39 IN W, Tensile Strength: 120 Lbs.

- Stainless Steel Barb Tie Nylon 6/6 Standard, Self-locking stainless steel barb, Maximum strength and adjustability for versatility

Product Details

General

Application	For use with self-locking stainless steel barb
Color	Black
Rating - Minimum Tensile Strength lbs	120
Sub Brand	UNIRAP,CABLE TIE
Trade Name	UNIRAP™
Type	CT_SSB
UPC	781810643136

Dimensions

Dimension - Bundle Diameter Max inch	3.15
Dimension - L Length Overall mm	300 mm
Dimension - Length Overall inch	11.81 in
Dimension - Width inch	0.39 in
Dimension - Width mm	10 mm

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - cULus	Y
Standards - RoHS Compliance Status	CM

Logistics

Carton Quantity	2000 EA
Minimum Pack Quantity	50

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)