

# CT120400D0

by Burndy  
Catalog ID: CT120400D0

Nylon 6/6 Standard Cable Tie, UV Black, 120 Lbs Min Ten Strgth, 15.25" L, 0.30" W.

- Standard Cable Tie
- Features: Cable Ties for General Use Available in Black or Natural, One piece injection molded, Installation Tool: TWT2, MK9 Tool



## Product Details

### General

Application	For Outdoor Applications
Color	Black
Material	Nylon 6/6
Operating Temperature Celcius Max	85 °C
Operating Temperature Celcius Min	-40 °C
Rating - Minimum Tensile Strength lbs	120
Sub Brand	UNIRAP,CABLE TIE
Trade Name	UNIRAP™
Type	Standard
UPC	781810333495

### Dimensions

Dimension - Bundle Diameter Max inch	4
Dimension - L Length Overall mm	383 mm
Dimension - Length Overall inch	15.09 in
Dimension - Width inch	0.3 in
Dimension - Width mm	8 mm

### Certifications and Compliance

Certification - 94V0 Rated	N
Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - UV Rated	Yes
Certification - cULus	No
Military Spec Number	MS3367-3-0
Standards - RoHS Compliance Status	CM
UL Listed	No

### Logistics

Carton Quantity	2000 EA
Minimum Pack Quantity	500

**For further technical assistance, please contact us**

**BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)