



CT120400LOUG

by Burndy
Catalog ID: CT120400LOUG

Nylon UNIRAP - 120 Lb. Tensile Strength

- Standard Cable Tie

Product Details

General

| | |
|---------------------------------------|--------------|
| Color | UV Black |
| Material | Nylon 6/6 |
| Rating - Minimum Tensile Strength lbs | 120 |
| Tool Type | Standard |
| Trade Name | UNIRAP™ |
| UPC | 781810469187 |

Dimensions

| | |
|--------------------------------------|----------|
| Dimension - Bundle Diameter Max inch | 4 |
| Dimension - L Length Overall mm | 370 mm |
| Dimension - Length Overall inch | 14.57 in |
| Dimension - Width inch | 0.28 in |
| Dimension - Width mm | 7 mm |

Certifications and Compliance

| | |
|------------------------------------|-----|
| Certification - CSA Approved | No |
| Certification - ETL | No |
| Certification - UL Recognized | No |
| Certification - UV Rated | Yes |
| Certification - cULus | No |
| Standards - RoHS Compliance Status | CM |
| UL Listed | No |

Logistics

| | |
|-----------------------|---------|
| Carton Quantity | 3000 EA |
| Minimum Pack Quantity | 50 |

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)