



CT120400L0

by Burndy
Catalog ID: CT120400L0

UV Black1 Nylon 6/6 Cable Tie, 4" Max. Bundle Dia, 120 Lbs, 15.25" Long, 0.30" Wide.

- Standard Cable Tie
- Features: Cable Ties for General Use Available in Black or Natural, One piece injection molded, Installation Tool: TWT2, MK9 Tool

Product Details

General

| | |
|---------------------------------------|--------------------------|
| Application | For Outdoor Applications |
| Color | UV Black |
| Material | Nylon 6/6 |
| Operating Temperature Celcius Max | 85 °C |
| Operating Temperature Celcius Min | -40 °C |
| Rating - Minimum Tensile Strength lbs | 120 |
| Sub Brand | UNIRAP,CABLE TIE |
| Tool Type | Standard |
| Trade Name | UNIRAP™ |
| Type | Standard |
| UPC | 781810333488 |

Dimensions

| | |
|--------------------------------------|----------|
| Dimension - Bundle Diameter Max inch | 4 |
| Dimension - L Length Overall mm | 383 mm |
| Dimension - Length Overall inch | 15.09 in |
| Dimension - Width inch | 0.30 in |
| Dimension - Width mm | 8 mm |

Certifications and Compliance

| | |
|------------------------------------|------------|
| Certification - 94V0 Rated | N |
| Certification - CSA Approved | No |
| Certification - ETL | No |
| Certification - UL Recognized | No |
| Certification - UV Rated | Yes |
| Certification - cULus | No |
| Military Spec Number | MS3367-3-0 |
| Standards - RoHS Compliance Status | CM |
| UL Listed | No |

Logistics

| | |
|-----------------|---------|
| Carton Quantity | 2000 EA |
|-----------------|---------|

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)