



CT120400MH14D

by Burndy
Catalog ID: CT120400MH14D

Screw Mount UNIRAP Cable Ties

- Mounting Hole

Product Details

General

Color	Natural
Material	Nylon 6/6
Mounting Method	Screw
Operating Temperature Celcius Max	85 °C
Operating Temperature Celcius Min	-40 °C
Rating - Minimum Tensile Strength lbs	120
Trade Name	UNIRAP™
UPC	781810335338

Dimensions

Dimension - Bundle Diameter Max inch	4
Dimension - L Length Overall mm	399 mm
Dimension - Length Overall inch	15.70 in
Dimension - Screw Size inch	0.25
Dimension - Width inch	0.30 in
Dimension - Width mm	8 mm

Certifications and Compliance

Certification - 94VO Rated	N
Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - UV Rated	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	1000 EA
Minimum Pack Quantity	1000
Packaging Type	Bag

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)