



CT120400MH14L

by Burndy
Catalog ID: CT120400MH14L

Nylon Natural Screw Mounting Cable Tie.

- Mounting Hole
- Features: Cable Ties for General Use Available in Black or Natural, One piece injection molded, Installation Tool: MK9 Tool, Stud Size: 1/4 IN (M6)

Product Details

General

Application	For Screw Mount
Color	Natural
Material	Nylon 6/6
Mounting Method	Screw
Operating Temperature Celcius Max	85 °C
Operating Temperature Celcius Min	-40 °C
Rating - Minimum Tensile Strength lbs	120
Sub Brand	UNIRAP,CABLE TIE
Trade Name	UNIRAP™
Type	Standard
UPC	781810335321

Dimensions

Dimension - Bundle Diameter Max inch	4
Dimension - L Length Overall mm	399 mm
Dimension - Length Overall inch	15.70 in
Dimension - Screw Size inch	1/4
Dimension - Width inch	0.30 in
Dimension - Width mm	8 mm

Certifications and Compliance

Certification - 94V0 Rated	N
Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - UV Rated	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	1000 EA
-----------------	---------

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)