



## CT120400SSBCO

by Burndy  
Catalog ID: CT120400SSBCO

Nylon Stainless Steel BARB Cable Ties, 15.75 IN L, .39 IN W, Tensile Strength: 120 Lbs, Installation tool: MK9, TWT2.

- Stainless Steel Barb Tie Nylon 6/6 Standard, Self-locking stainless steel barb, Maximum strength and adjustability for versatility

## Product Details

### General

Application	For use with self-locking stainless steel barb
Color	Black
Material	Nylon 6/6
Rating - Minimum Tensile Strength N	124
Sub Brand	UNIRAP,CABLE TIE
Trade Name	UNIRAP™
Type	CT_SSB
UPC	781810565063

### Dimensions

Dimension - Bundle Diameter Max inch	4.33
Dimension - L Length Overall mm	400 mm
Dimension - Length Overall inch	15.75 in
Dimension - Width mm	0 mm

### Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - cULus	Y
Standards - RoHS Compliance Status	CM

### Logistics

Minimum Pack Quantity	100
-----------------------	-----

For further technical assistance, please contact us

**BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)