


CT1751100Q

by Burndy
Catalog ID: CT1751100Q

Nylon cable ties, Tensile strength-175 Lbs, Color- Natural, 36.50"L,
0.34"W, 11.00" Bundle Dia.

- Standard Cable Tie



Product Details

General

Color	Natural
Material	Nylon 6/6
Operating Temperature Celcius Max	85 °C
Operating Temperature Celcius Min	0 °C
Rating - Minimum Tensile Strength lbs	175
Tool Type	Heavy
Trade Name	UNIRAP™
UPC	781810333853

Dimensions

Dimension - Bundle Diameter Max inch	11
Dimension - L Length Overall mm	927 mm
Dimension - Length Overall inch	36.50 in
Dimension - Width inch	0.34 in
Dimension - Width mm	8.6 mm

Certifications and Compliance

Certification - 94V0 Rated	N
Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	Yes
Certification - UV Rated	No
Certification - cULus	No
Military Spec Number	MS3367-13-9
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	500 EA
Minimum Pack Quantity	25
Packaging Type	Bag

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)