



CT1751400Q0

by Burndy
Catalog ID: CT1751400Q0

Nylon cable ties, Tensile strength-175 Lbs, Color- UV Black, 48.00"L,
0.35"W, 15.00" Bundle Dia.

- Standard Cable Tie

Product Details

General

Color	UV Black
Material	Nylon 6/6
Operating Temperature Celcius Max	85 °C
Operating Temperature Celcius Min	-40 °C
Rating - Minimum Tensile Strength lbs	175
Tool Type	Heavy
Trade Name	UNIRAP™
UPC	781810334140

Dimensions

Dimension - Bundle Diameter Max inch	15
Dimension - L Length Overall mm	1219 mm
Dimension - Length Overall inch	48.00 in
Dimension - Width inch	0.35 in
Dimension - Width mm	8.9 mm

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	Yes
Certification - UV Rated	Yes
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	500 EA
Minimum Pack Quantity	500
Packaging Type	Bag

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)