



CT175500Q0

by Burndy
Catalog ID: CT175500Q0

UNIRAP, CT-Q, Standard Cable Ties, Installation Tool: TWT2, MK9, CTT50 Tool, For general purpose applications, RoHS Under InvestigationMaterial: Nylon 6/6 UV.

- Standard Cable Tie
Bundle Diameter: 5.50 IN Maximum

Product Details

General

Application	For general purpose applications
Color	UV Black
Material	Nylon 6/6
Operating Temperature Celcius Max	85 °C
Operating Temperature Celcius Min	32 °C
Rating - Minimum Tensile Strength lbs	175
Sub Brand	UNIRAP
Tool Type	Heavy
Trade Name	UNIRAP™
Type	Cable Ties
UPC	781810661116

Dimensions

Dimension - Bundle Diameter Max inch	5.50
Dimension - L Length Overall mm	460 mm
Dimension - Length Overall inch	18.10 in
Dimension - Width inch	0.34 in
Dimension - Width mm	8.6 mm

Certifications and Compliance

Certification - CSA Approved	No
Certification - UL Recognized	Yes
Certification - UV Rated	Yes
Certification - cULus	No
Standards - RoHS Compliance Status	CM

Logistics

Carton Quantity	1000 EA
Minimum Pack Quantity	25

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)