

## CT175600Q0UG

by Burndy  
Catalog ID: CT175600Q0UG

Universal grade cable Ties, Nylon 6/6 UV Stabilized, 175 Lbs, 21" L, UV Black, 6" Bundle Dia, Package: 25.

- Standard Cable Tie  
Nylon 6/6 Standard, One piece injection molded, Maximum strength and adjustability for versatility, Chemically resistant to solvents,oils,grease, and diluted acids, Rounded edges and bent tip for easy installation, Self-Locking



## Product Details

### General

Application	For both field and production line use
Color	UV Black
Material	Nylon 6/6
Rating - Minimum Tensile Strength lbs	175
Sub Brand	CABLE TIE
Tool Type	Heavy
Trade Name	UNIRAP™
Type	CT_UG
UPC	781810499160

### Dimensions

Dimension - Bundle Diameter Max inch	6
Dimension - L Length Overall mm	610 mm
Dimension - Length Overall inch	24.00 in
Dimension - Width inch	0.35 in
Dimension - Width mm	8.9 mm

### Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - UV Rated	Yes
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

### Logistics

Carton Quantity	1500 EA
Minimum Pack Quantity	25

For further technical assistance, please contact us

**BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)