

CT175600Q

by Burndy
Catalog ID: CT175600Q

Natural Nylon 6/6 Cable Tie, 6" Max. Bundle Dia, 175 Lbs, 21" Long, 0.35" Wide.

- Standard Cable Tie
- Features: Cable Ties for General Use Available in Black or Natural, One piece injection molded, Installation Tool: TWT2, MK9 Tool



Product Details

General

Application	For General Purpose
Color	Natural
Material	Nylon 6/6
Military Specification	MS3367
Operating Temperature Celcius Max	85 °C
Operating Temperature Celcius Min	0 °C
Rating - Minimum Tensile Strength lbs	175
Sub Brand	UNIRAP,CABLE TIE
Tool Type	Heavy
Trade Name	UNIRAP™
Type	Heavy
UPC	781810333631

Dimensions

Dimension - Bundle Diameter Max inch	7
Dimension - L Length Overall mm	622 mm
Dimension - Length Overall inch	24.51 in
Dimension - Width inch	0.35 in
Dimension - Width mm	8.9 mm

Certifications and Compliance

Certification - 94V0 Rated	N
Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	Yes
Certification - UV Rated	No
Certification - cULus	No
Industry Standard(s)	Military Specified (Mil-Spec)
Military Spec Number	MS3367-10-9
Standards - Industry Standards Met	Military Specified (Mil-Spec)
Standards - RoHS Compliance Status	CM

UL Listed	No
-----------	----

Logistics

Carton Quantity	500 EA
Minimum Pack Quantity	25

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)