



CT175800Q0

by Burndy
Catalog ID: CT175800Q0

Nylon cable tie, Tensile strength: 175lb, Bundle dia: 8.

- Standard Cable Tie
- Cable Ties for General Use Available in Black or Natural, One piece injection molded, Installation Tool: TWT2, MK9 Tool

Product Details

General

Application	For connecting cable to ground rod
Color	UV Black
Material	Nylon 6/6
Operating Temperature Celcius Max	85 °C
Operating Temperature Celcius Min	0 °C
Rating - Minimum Tensile Strength lbs	175
Sub Brand	UNIRAP
Tool Type	Heavy
Trade Name	UNIRAP™
Type	STANDARD
UPC	781810661123

Dimensions

Dimension - Bundle Diameter Max inch	8.90
Dimension - L Length Overall mm	830 mm
Dimension - Length Overall inch	32.67 in
Dimension - Width inch	0.35 in
Dimension - Width mm	8.9 mm

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	Yes
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	500 EA
Minimum Pack Quantity	25

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)