



## CT18075FLC

by Burndy  
Catalog ID: CT18075FLC

Nylon cable ties, Tensile strength-18 Lbs, Color- Natural, 04.10"L, 0.10"W, 0.75" Bundle Dia.

- Identification

## Product Details

### General

Color	Natural
Material	Nylon 6/6
Rating - Minimum Tensile Strength lbs	18 lb
Trade Name	UNIRAP™
UPC	781810335376

### Dimensions

Dimension - Bundle Diameter Max inch	0.75
Dimension - L Length Overall mm	104 mm
Dimension - Length Overall inch	4.10 in
Dimension - Marking Pad Size inch	0.36 X 0.81
Dimension - Width inch	0.10 in
Dimension - Width mm	2.5 mm

### Certifications and Compliance

Certification - 94V0 Rated	N
Certification - CSA Approved	No
Certification - UV Rated	No
Standards - RoHS Compliance Status	CM

### Logistics

Carton Quantity	20000 EA
Minimum Pack Quantity	1000

**For further technical assistance, please contact us**

**BURNDY Headquarters**  
47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**  
8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)