



CT18200COUG

by Burndy
Catalog ID: CT18200COUG

Nylon UNIRAP - 18 Lb. Tensile Strength

- Standard Cable Tie

Product Details

General

Color	UV Black
Material	Nylon 6/6
Rating - Minimum Tensile Strength N	18
Rating - Minimum Tensile Strength lbs	18
Tool Type	Mini
Trade Name	UNIRAP™
UPC	781810512135
UPC 12 Digit	7818105121355

Dimensions

Dimension - Bundle Diameter Max inch	2
Dimension - L Length Overall mm	202 mm
Dimension - Length Overall inch	7.95 in
Dimension - Width inch	0.10 in
Dimension - Width mm	3 mm

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	Yes
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	21000 EA
Minimum Pack Quantity	100

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)