



CT18200SSBC

by Burndy
Catalog ID: CT18200SSBC

Nylon Stainless Steel BARB Cable Ties, 7.91 IN L, .09 IN W, Tensile Strength: 18 Lbs, Color: Natural.

- Stainless Steel Barb Tie Nylon 6/6 Standard, Self-locking stainless steel barb, Maximum strength and adjustability for versatility

Product Details

General

| | |
|---------------------------------------|--|
| Application | For use with self-locking stainless steel barb |
| Color | Natural |
| Material | Nylon 6/6 |
| Rating - Minimum Tensile Strength lbs | 18 |
| Sub Brand | UNIRAP,CABLE TIE |
| Trade Name | UNIRAP™ |
| Type | CT_SSB |
| UPC | 781810564448 |

Dimensions

| | |
|--------------------------------------|---------|
| Dimension - Bundle Diameter Max inch | 2.01 |
| Dimension - L Length Overall mm | 201 mm |
| Dimension - Length Overall inch | 7.91 in |
| Dimension - Width inch | 0.09 in |
| Dimension - Width mm | 2 mm |

Certifications and Compliance

| | |
|------------------------------------|-----|
| Certification - CSA Approved | Yes |
| Certification - ETL | No |
| Certification - cULus | Y |
| Standards - RoHS Compliance Status | EX |

Logistics

| | |
|-----------------------|---------|
| Carton Quantity | 3000 EA |
| Minimum Pack Quantity | 100 |

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)