



CT2501000Q

by Burndy
Catalog ID: CT2501000Q

Nylon cable ties, Tensile strength-250 Lbs, Color- Natural, 34.60"L,
0.50"W, 9.53" Bundle Dia.

- Standard Cable Tie

Product Details

General

Color	Natural
Material	Nylon 6/6
Operating Temperature Celcius Max	85 °C
Operating Temperature Celcius Min	-40 °C
Rating - Minimum Tensile Strength lbs	250
Tool Type	Heavy
Trade Name	UNIRAP™
UPC	781810334393

Dimensions

Dimension - Bundle Diameter Max inch	9.53 in
Dimension - L Length Overall mm	879 mm
Dimension - Length Overall inch	34.64 in
Dimension - Width inch	0.50 in
Dimension - Width mm	13 mm

Certifications and Compliance

Certification - 94V0 Rated	N
Certification - CSA Approved	No
Certification - UV Rated	No
Standards - RoHS Compliance Status	CM

Logistics

Carton Quantity	500 EA
Minimum Pack Quantity	250
Packaging Type	Bag

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)