



## CT2501000RQ

by Burndy  
Catalog ID: CT2501000RQ

Nylon cable ties, Tensile strength-250 Lbs, Color- Natural, 34.00"L,  
0.50"W, 10.00" Bundle Dia.

- Releaseable

## Product Details

### General

Color	Natural
Material	Nylon 6/6
Operating Temperature Celcius Max	85 °C
Operating Temperature Celcius Min	-40 °C
Rating - Minimum Tensile Strength lbs	250
Trade Name	UNIRAP™
UPC	781810334881

### Dimensions

Dimension - Bundle Diameter Max inch	10
Dimension - L Length Overall mm	864 mm
Dimension - Length Overall inch	34.00 in
Dimension - Width inch	0.50 in
Dimension - Width mm	13 mm

### Certifications and Compliance

Certification - 94V0 Rated	N
Certification - CSA Approved	No
Certification - UV Rated	No
Standards - RoHS Compliance Status	CM

### Logistics

Carton Quantity	1000 EA
Minimum Pack Quantity	1000
Packaging Type	Bag

**For further technical assistance, please contact us**

**BURNDY Headquarters**  
47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**  
8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)