



## CT30125MH8M0

by Burndy  
Catalog ID: CT30125MH8M0

Nylon cable ties, Tensile strength-30 Lbs, Color- UV Black, 05.80"L,  
0.13"W, 01.25" Bundle Dia.

- Mounting Hole

### Product Details

#### General

Color	Black
Material	Nylon 6/6
Mounting Method	Screw
Operating Temperature Celcius Max	85 °C
Operating Temperature Celcius Min	-40 °C
Rating - Minimum Tensile Strength lbs	30
Trade Name	UNIRAP™
UPC	781810335239

#### Dimensions

Dimension - Bundle Diameter Max inch	1.25
Dimension - L Length Overall mm	147 mm
Dimension - Length Overall inch	5.80 in
Dimension - Screw Size inch	#8
Dimension - Width inch	0.13 in
Dimension - Width mm	3 mm

#### Certifications and Compliance

Certification - 94VO Rated	N
Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - UV Rated	Yes
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

#### Logistics

Carton Quantity	10000 EA
Minimum Pack Quantity	1000
Packaging Type	Bag

**For further technical assistance, please contact us**

**BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)